

84010007 Cut Sheet



GAM helical pinion, Module 2, 26 tooth, bolt-through mount. For use with SureGear PGD064 series gearboxes.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/84010007>

Technical Specifications

Brand	GAM
Item	Pinion
Tooth Profile	Helical
Pressure Angle	20 degrees
Module	2
Pitch Diameter	55.174mm
Number of Teeth	26
Travel per Rotation	173.334mm
Maximum Force Feed	13.4 kN
Mounting	Bolt-through
Mounting Distance	50.4mm
Material	4140 carbon steel
Hardness	55 - 60 HRC
Finish	Ra 0.8
Precision Grade	ISO Q06
For Use With	SureGear PGD064 series gearboxes

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document