


# 859-805 Cut Sheet



WAGO DC to DC converter, 10-30 VDC input, 12 VDC output, 0.5A, 6W, plastic housing, 35mm DIN rail mount, cage clamp.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/859-805>

## Technical Specifications

<b>Brand</b>	WAGO
<b>Item</b>	DC to DC converter
<b>Input voltage range</b>	10-30 VDC
<b>Output Voltage Range</b>	12 VDC
<b>Load Current</b>	0.5A
<b>Output Power</b>	6W
<b>Housing Material</b>	Plastic
<b>Encapsulated</b>	No
<b>Mounting</b>	35mm DIN rail
<b>Terminal Block Type</b>	Cage clamp
<b>Removable</b>	No

## Agency Approvals

<b>UL Listed File #</b>	E175199
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/859-805.pdf>  
See store item page for other formats.