

862504001 Cut Sheet



Seifert SlimLine Vario air conditioner, 8700 BTU/H, R-134a, 115/230 VAC operating voltage, carbon steel housing, RAL 7035 light gray, filter-free, side mount. For use with NEMA 12 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/862504001>

Technical Specifications

Brand	Seifert
Series	SlimLine Vario
Item	Air conditioner
Nominal Cooling Capacity	8700 BTU/H
Operating Voltage	115/230 VAC
Frequency	50/60 Hz
Running Current	12.6A/6.3A
Refrigerant	R-134a
Height	53.15in
Width	15.75in
Depth	8.27in

Mounting	Side
Filter-Free	Yes
Housing Material	Carbon steel
Color	RAL 7035 light gray
IP Rating	IP55
For Use With	NEMA 12 enclosures
Includes	Mounting template and hardware
Dangerous Goods	<ul style="list-style-type: none">• Packaging Instructions: 200• UN Number: 3159• Hazard Type: Compressed Gas

Agency Approvals

UL Listed File #	SA32278
UL Recognized File #	E498756
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/862504001.pdf>
See store item page for other formats.