


908168 Cut Sheet



Dehn EZ50-S series power Surge Protective Device (SPD), 20 kA discharge current, 480/277 VAC 3-Phase Wye, neutral ground protection, parallel circuit, NEMA 4X enclosure rating, IP66, 1/2in NPSM/Wall mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/908168>

Technical Specifications

| | |
|---------------------------------|---|
| Brand | Dehn |
| Item | Surge Protective Device (SPD) |
| Series | EZ50-S |
| Surge Protection Type | Power protection |
| UL Type | UL Type 1 |
| Circuit Type | Parallel circuit |
| Neutral Ground Protection | Yes |
| System Voltage | 480/277 VAC 3-Phase Wye |
| Nominal Discharge Current | 20 kA |
| Voltage Protection Rating (VPR) | 2500V (L-L), 1200V (L-N), 1800V (L-G), 700V (N-G) |

| | |
|------------------------------|-----------------------------------|
| Per Phase Max Surge Capacity | 50 kA |
| Indicating Type | Red/green indicating flag |
| SCCR Rating | 200kA SCCR |
| UL Rating | UL 1449 rated |
| Enclosure Rating | NEMA 4X |
| IP Rating | IP66 |
| Mounting | 1/2in NPSM/Wall |
| Connection | 4-wire with ground 10 AWG pigtail |
| Includes | Wall/panel mounting hardware |

Agency Approvals

| | |
|----------------------|---|
| UL Listed File # | E319777 |
| UL Recognized File # | N/A |
| UL Hazardous File # | N/A |
| CSA File # | N/A |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/908168.pdf>
See store item page for other formats.