

9165-16-11-11S Cut Sheet



STAHL intrinsically safe analog output isolator, 0-20 mA or 4-20 mA input, 0-20 mA or 4-20 mA output, 24 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9165-16-11-11S>

Technical Specifications

Brand	STAHL
Item	Isolator
Isolator Type	Analog output
Intrinsically Safe	Yes
Input	0-20 mA or 4-20 mA
Output	0-20 mA or 4-20 mA
Maximum Voltage	25.6 VDC
Maximum Current	96 mA
Maximum Power	605 mW
Operating Voltage	24 VDC
Housing Material	Polyamide
Mounting	35mm DIN rail
Connection	Screw terminals
Application	Hazardous location rated
Additional Information	Manufacturer part number: 9165/16-11-11s

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	FM Approval Document