

9275-10-24-48-11S Cut Sheet



STAHL ISpac intrinsically safe digital output isolator, 15-30 VDC input, 48 mA at 9.7 VDC output, 24 VDC operating voltage, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9275-10-24-48-11S>

Technical Specifications

Brand	STAHL	Maximum Current	91.11 mA
Series	ISpac	Maximum Power	616 mW
Item	Isolator	Operating Voltage	24 VDC
Isolator Type	Digital output	Housing Material	Polyamide
Intrinsically Safe	Yes	Mounting	35mm DIN rail
Input	15-30 VDC	Connection	Screw terminals
Output	48 mA at 9.7 VDC	Application	Hazardous location rated
Maximum Voltage	27.06 VDC	Manufacturer Part Number	9275/10-24-48-11s

Agency Approvals

UL Listed File #	E81680
UL Recognized File #	None
UL Hazardous File #	E81680
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/9275-10-24-48-11S.pdf>
See store item page for other formats.