


# 929963 Cut Sheet



Dehn DPI-CD series data & signal Surge Protective Device (SPD), 24VAC/VDC, parallel circuit, 2 lines or 1 pair, IP67, 1/2in-14 NPSM mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/929963>

## Technical Specifications

<b>Brand</b>	Dehn
<b>Item</b>	Surge Protective Device (SPD)
<b>Series</b>	DPI-CD
<b>Surge Protection Type</b>	Data & signal protection
<b>Signal Types Protected</b>	0-20mA, 4-20mA, Fieldbus systems, intrinsically safe signals
<b>Circuit Type</b>	Parallel circuit
<b>Channels</b>	2 lines or 1 pair
<b>Neutral Ground Protection</b>	No

<b>System Voltage</b>	24VAC/VDC
<b>Voltage Protection Rating (VPR)</b>	58V (L-L), 1700V (L-G)
<b>Housing Material</b>	Stainless steel
<b>IP Rating</b>	IP67
<b>Mounting</b>	1/2in-14 NPSM
<b>Connection</b>	3-wire 16 AWG pigtail
<b>Application</b>	Hazardous location rated

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	215727
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/929963.pdf>  
See store item page for other formats.