

# 96200103 Cut Sheet



LS Electric high-precision planetary gearbox, 20:1 ratio, inline, 22mm diameter output shaft, nominal output torque 143 N-m (1266 lb-in), 2-stage, 90mm frame. For use with FBL series 100W, 200W and 400W motors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/96200103>

## Technical Specifications

<b>Brand</b>	LS Electric
<b>Item</b>	Gearbox
<b>Application</b>	High-precision
<b>Gearbox Type</b>	Planetary
<b>Gear Ratio</b>	20:1
<b>Output Configuration</b>	Inline
<b>Gearbox Output Shaft Diameter</b>	22mm
<b>Nominal Output Torque</b>	Nominal output torque 143 N-m (1266 lb-in)
<b>Number of Stages</b>	2
<b>Frame</b>	90mm
<b>For Use With</b>	FBL series 100W, 200W and 400W motors
<b>Includes</b>	Input adapter bushing, motor mounting hardware and output shaft key
<b>Manufacturer Part Number</b>	MSS0902B-020KS-B3110103C14

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>