

A-GFI-1214-12 Cut Sheet



igus iglide series plain bearing, type G300 polymer, 3/4in inside diameter, 7/8in outside diameter, 3/4in overall length, flanged. Package of 5. For use with 3/4in diameter drylin R series shafts.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A-GFI-1214-12>

Technical Specifications

Brand	igus
Item	Plain bearing
Series	Iglide
Bearing Material	Type G300 polymer
Bearing Inside Diameter	3/4in
Bearing Outside Diameter	7/8in
Overall Length	3/4in
Flanged	Yes
Flange Outside Diameter	1-1/8in
Quantity per Pack	5
For Use With	3/4in diameter drylin R series shafts
Application	General purpose

Agency Approvals

CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/A-GFI-1214-12.pdf>
See store item page for other formats.