

# A-TFI-0405-04 Cut Sheet



igus iglide series plain bearing, type T500 polymer, 1/4in inside diameter, 5/16in outside diameter, 1/4in overall length, flanged. Package of 5. For use with 1/4in diameter drylin R series shafts.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A-TFI-0405-04>

## Technical Specifications

Brand	igus
Item	Plain bearing
Series	Iglide
Bearing Material	Type T500 polymer
Bearing Inside Diameter	1/4in
Bearing Outside Diameter	5/16in
Overall Length	1/4in
Flanged	Yes
Flange Outside Diameter	1/2in
Quantity per Pack	5
For Use With	1/4in diameter drylin R series shafts
Application	Chemical resistant, high temperatures

## Agency Approvals

CE	<a href="#">View CE declarations</a>
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/A-TFI-0405-04.pdf>  
See store item page for other formats.