

A-TSI-0405-04 Cut Sheet



igus iglide series plain bearing, type T500 polymer, 1/4in inside diameter, 5/16in outside diameter, 1/4in overall length. Package of 5. For use with 1/4in diameter drylin R series shafts.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A-TSI-0405-04>

Technical Specifications

Brand	igus
Item	Plain bearing
Series	Iglide
Bearing Material	Type T500 polymer
Bearing Inside Diameter	1/4in
Bearing Outside Diameter	5/16in
Overall Length	1/4in
Flanged	No
Quantity per Pack	5
For Use With	1/4in diameter drylin R series shafts
Application	Chemical resistant, high temperatures

Agency Approvals

CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/A-TSI-0405-04.pdf>
See store item page for other formats.