

# AAM2F53Z11 Cut Sheet



AutomationDirect IEC limit switch, side rotary adjustable metal lever with 18mm metal roller, 90-degree adjustable head, (1) N.O./ (1) N.C. contact(s), snap action, 20-22mm hole spacing, zinc alloy, 1/2in NPT cable entry.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AAM2F53Z11>

## Technical Specifications

<b>Brand</b>	AutomationDirect
<b>Item</b>	Limit switch
<b>Switch Type</b>	IEC
<b>Actuator Type</b>	Side rotary adjustable metal lever with 18mm metal roller
<b>Head Type</b>	90-degree adjustable
<b>Contact Type</b>	(1) N.O./ (1) N.C.
<b>Action</b>	Snap action
<b>Reset</b>	No
<b>Body Width</b>	30.3mm
<b>Mounting Hole Spacing</b>	20-22mm
<b>Material</b>	Zinc alloy
<b>IP Rating</b>	IP66
<b>Operating Temperature</b>	-10 to 70 deg C
<b>Connection</b>	1/2in NPT cable entry

## Agency Approvals

<b>UL Listed File #</b>	E191072
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>