

# AAP2T14Z11 Cut Sheet



AutomationDirect IEC limit switch, galvanized steel plunger, 90-degree adjustable head, (1) N.O./ (1) N.C. contact(s), snap action, 20-22mm hole spacing, plastic, (1) PG11 cable entry with 1/2in NPT adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AAP2T14Z11>

## Technical Specifications

|                       |   |
|-----------------------|---|
| Brand                 | AutomationDirect                            |
| Item                  | Limit switch                                |
| Switch Type           | IEC   |
| Actuator Type         | Galvanized steel plunger                    |
| Head Type             | 90-degree adjustable                        |
| Contact Type          | (1) N.O./ (1) N.C.                          |
| Action                | Snap action                                 |
| Reset                 | No  |
| Body Width            | 30.3mm                                      |
| Mounting Hole Spacing | 20-22mm                                     |
| Material              | Plastic                                     |
| IP Rating             | IP65  |
| Operating Temperature | -25 to 70 deg C                             |
| Connection            | (1) PG11 cable entry with 1/2in NPT adapter |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | E191072                                |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | <a href="#">View CE declarations</a>   |
| RoHS Status          | Yes (See CE Doc)                       |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/AAP2T14Z11.pdf>  
See store item page for other formats.