

AAP7T35Z11 Cut Sheet



AutomationDirect IEC limit switch, one-way horizontal lever with polyamide roller, 90-degree adjustable head, (1) N.O./(1) N.C. contact(s), snap action, 20-22mm hole spacing, plastic, 5-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AAP7T35Z11>

Technical Specifications

| | |
|------------------------------|--|
| Brand | AutomationDirect |
| Item | Limit switch |
| Switch Type | IEC |
| Actuator Type | One-way horizontal lever with polyamide roller |
| Head Type | 90-degree adjustable |
| Contact Type | (1) N.O./(1) N.C. |
| Action | Snap action |
| Reset | No |
| Body Width | 30.3mm |
| Mounting Hole Spacing | 20-22mm |
| Material | Plastic |
| IP Rating | IP65 |
| Operating Temperature | -25 to 70 deg C |
| Connection | 5-pin M12 quick-disconnect |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E191072 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |