

# ABP1H41Z11 Cut Sheet



AutomationDirect IEC limit switch, side rotary lever with polyamide roller, 90-degree adjustable head, (1) N.O./(1) N.C. contact(s), snap action, 30mm hole spacing, plastic, (1) PG13.5 cable entry.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ABP1H41Z11>

## Technical Specifications

<b>Brand</b>	AutomationDirect
<b>Item</b>	Limit switch
<b>Switch Type</b>	IEC
<b>Actuator Type</b>	Side rotary lever with polyamide roller
<b>Head Type</b>	90-degree adjustable
<b>Contact Type</b>	(1) N.O./(1) N.C.
<b>Action</b>	Snap action
<b>Reset</b>	No
<b>Body Width</b>	41mm
<b>Mounting Hole Spacing</b>	30mm
<b>Material</b>	Plastic
<b>IP Rating</b>	IP65
<b>Operating Temperature</b>	-25 to 70 deg C
<b>Connection</b>	(1) PG13.5 cable entry

## Agency Approvals

<b>UL Listed File #</b>	E191072
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>