

ACE202410LG Cut Sheet



Hammond Aluminum Command series HMI Enclosure, NEMA 12/13, 20 x 24 x 10in (HxWxD), suspension mount, aluminum, RAL 7035 light gray, powder coat finish, single-door, 1/4-turn semi-flush.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ACE202410LG>

Technical Specifications

Brand	Hammond
Item	HMI Enclosure
Series	Aluminum Command
Subpanel	Purchase subpanel separately
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	12/13
IP Rating	IP54
Nominal Enclosure Dimensions	20 x 24 x 10in (HxWxD)
Mounting	Suspension
Dual Access	No

Knockouts	No
Material	Aluminum
Color	RAL 7035 light gray
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	2
Latch Type	1/4-turn semi-flush
Number Of Latches	2
Padlockable	No
Keylocking	No
Includes	Heavy-duty reinforcing plate

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/ACE202410LG.pdf>
See store item page for other formats.