

# ACN-ECAT Cut Sheet



IronHorse ACN series communication module, EtherCAT Slave, 2 ports, (2) Ethernet (RJ45) port(s). For use with IronHorse ACN series AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ACN-ECAT>

## Technical Specifications

<b>Brand</b>	IronHorse
<b>Item</b>	Communication module
<b>Series</b>	ACN
<b>Number of Ports</b>	2
<b>Buffered Ports</b>	No
<b>Communication Port and Connection Type(s)</b>	(2) Ethernet (RJ45)
<b>Port Protocol(s)</b>	EtherCAT Slave
<b>Port Speed(s)</b>	100 Mbps auto-detect
<b>For Use With</b>	IronHorse ACN series AC drives

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/ACN-ECAT.pdf>  
See store item page for other formats.