

# ACS200-AA3-FT Cut Sheet



AcuAMP AC current switch, fixed core, 1-6, 6-40, or 40-175A selectable sensing range, 1-175A adjustable trip point, 15-turn potentiometer, solid state switch, N.O. output, 3A @ 120 VAC output rating.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ACS200-AA3-FT>

## Technical Specifications

<b>Brand</b>	AcuAMP
<b>Item</b>	Current switch
<b>Voltage Type</b>	AC
<b>Body Type</b>	Fixed core
<b>Sensing Range</b>	1-6, 6-40, or 40-175A selectable
<b>Trip Point</b>	1-175A adjustable
<b>Trip Point Adjustment</b>	15-turn potentiometer
<b>Output</b>	Solid state switch, N.O.
<b>Output Rating</b>	3A @ 120 VAC
<b>Operating Voltage</b>	Self powered
<b>Mounting</b>	Panel or optional 35mm DIN rail
<b>Electrical Connection</b>	Screw terminals
<b>UL Rating</b>	UL 508 listed

## Agency Approvals

<b>UL Listed File #</b>	E222847
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/ACS200-AA3-FT.pdf>  
See store item page for other formats.