

AD-HSSR810-DC-60 Cut Sheet



AutomationDirect solid state relay, 35mm DIN rail mount, finger-safe, 3-32 VDC input voltage, SPST, (1) N.O. SCR, 10A contact rating, 48-600 VAC load voltage, zero cross, screw terminal(s), LED indicator(s), hazardous location certified.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AD-HSSR810-DC-60>

Technical Specifications

Brand	AutomationDirect
Item	Relay
Relay Type	Solid state
Mounting	35mm DIN rail
Relay Housing Type	Finger-safe
Input Voltage	3-32 VDC
Relay Configuration	SPST
Output Type	(1) N.O. SCR
Load Voltage	48-600 VAC
Contact Rating	10A
Switching Type	Zero cross
Connector Type	Screw terminal(s)
Indicator	LED
Application	Hazardous location certified

Agency Approvals

UL Listed File #	None
UL Recognized File #	E344125
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/AD-HSSR810-DC-60.pdf>
See store item page for other formats.