

ADM2F11Z11 Cut Sheet



AchieVe IEC limit switch, metal plunger, 90-degree adjustable head, (1) N.O./ (1) N.C. contact(s), snap action, 20-22mm or 40-42mm hole spacing, zinc alloy, (3) 1/2in NPT entries.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ADM2F11Z11>

Technical Specifications

| | |
|------------------------------|-----------------------|
| Brand | AchieVe |
| Item | Limit switch |
| Switch Type | IEC |
| Actuator Type | Metal plunger |
| Head Type | 90-degree adjustable |
| Contact Type | (1) N.O./ (1) N.C. |
| Action | Snap action |
| Body Width | 52mm |
| Mounting Hole Spacing | 20-22mm or 40-42mm |
| Material | Zinc alloy |
| IP Rating | IP66 |
| Operating Temperature | -25 to 70 deg C |
| Connection | (3) 1/2in NPT entries |
| Halogen Free | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | NKCR.E191072 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/ADM2F11Z11.pdf>
See store item page for other formats.