

ADM2F12Z11 Cut Sheet



AchieVe IEC limit switch, metal plunger with metal roller, 90-degree adjustable head, (1) N.O./ (1) N.C. contact(s), snap action, 20-22mm or 40-42mm hole spacing, zinc alloy, (3) 1/2in NPT entries.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ADM2F12Z11>

Technical Specifications

Brand	AchieVe
Item	Limit switch
Switch Type	IEC
Actuator Type	Metal plunger with metal roller
Head Type	90-degree adjustable
Contact Type	(1) N.O./ (1) N.C.
Action	Snap action
Reset	No
Body Width	52mm
Mounting Hole Spacing	20-22mm or 40-42mm
Material	Zinc alloy
IP Rating	IP66
Operating Temperature	-25 to 70 deg C
Connection	(3) 1/2in NPT entries
Halogen Free	No

Agency Approvals

UL Listed File #	NKCR.E191072
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document