

# AEM2G7320Z11M Cut Sheet



AutomationDirect compact limit switch, side rotary adjustable 6mm nylon rod, (1) N.O./(1) N.C. contact(s), snap action, 25mm hole spacing, zinc alloy, 5-pin M12 quick-disconnect, bottom exit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AEM2G7320Z11M>

## Technical Specifications

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Brand</b>                 | AutomationDirect                     |
| <b>Item</b>                  | Limit switch                         |
| <b>Switch Type</b>           | Compact                              |
| <b>Actuator Type</b>         | Side rotary adjustable 6mm nylon rod |
| <b>Contact Type</b>          | (1) N.O./(1) N.C.                    |
| <b>Action</b>                | Snap action                          |
| <b>Reset</b>                 | No                                   |
| <b>Body Width</b>            | 35mm                                 |
| <b>Mounting Hole Spacing</b> | 25mm                                 |
| <b>Material</b>              | Zinc alloy                           |
| <b>IP Rating</b>             | IP67                                 |
| <b>Operating Temperature</b> | -25 to 70 deg C                      |
| <b>Connection</b>            | 5-pin M12 quick-disconnect           |
| <b>Cable Exit</b>            | Bottom                               |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E191072                                |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |