

# AEM2G93Z11-3 Cut Sheet



AutomationDirect compact limit switch, 360 degree stainless steel spring, (1) N.O./(1) N.C. contact(s), snap action, 25mm hole spacing, zinc alloy, pigtail, 9.8ft/3m cable length, bottom exit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AEM2G93Z11-3>

## Technical Specifications

<b>Brand</b>	AutomationDirect
<b>Item</b>	Limit switch
<b>Switch Type</b>	Compact
<b>Actuator Type</b>	360 degree stainless steel spring
<b>Contact Type</b>	(1) N.O./(1) N.C.
<b>Action</b>	Snap action
<b>Reset</b>	No
<b>Body Width</b>	35mm
<b>Mounting Hole Spacing</b>	25mm

<b>Material</b>	Zinc alloy
<b>IP Rating</b>	IP67
<b>Operating Temperature</b>	-25 to 70 deg C
<b>Connection</b>	Pigtail
<b>Conductor Size</b>	18 AWG
<b>Jacket Material</b>	PVC
<b>Cable Length</b>	9.8ft/3m
<b>Cable Exit</b>	Bottom

## Agency Approvals

<b>UL Listed File #</b>	E191072
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/AEM2G93Z11-3.pdf>  
See store item page for other formats.