

# AFR-3333-AD Cut Sheet



NITRA pneumatic filter-regulator, 3/8in female NPT inlet(s), 3/8in female NPT outlet(s), 20-130 psi adjustable range, automatic drain, die-cast aluminum bowl, sight gauge. For use with Ax-33 series air prep components.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AFR-3333-AD>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Filter-regulator
<b>Working Fluid</b>	Air or inert gas
<b>Inlet Port</b>	3/8in female NPT
<b>Outlet Port</b>	3/8in female NPT
<b>Pressure Range</b>	20-130 psi adjustable
<b>Drain Type</b>	Automatic
<b>Bowl Material</b>	Die-cast aluminum

<b>Bowl Guard</b>	No
<b>Sight Gauge</b>	Yes
<b>Flow Coefficient</b>	3.7
<b>For Use With</b>	Ax-33 series air prep components
<b>Includes</b>	Integral pressure gauge, locking adjustment knob, replaceable 40 micron filter element and mounting bracket

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/AFR-3333-AD.pdf>  
See store item page for other formats.