

AH12104HW Cut Sheet



AttaBox Heartland SL series enclosure, NEMA 1/3R/4/4X/6P/12, 12 x 10 x 4in (HxWxD), wall mount, polycarbonate, Pantone 7541 C light gray, hinged screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AH12104HW>

Technical Specifications

Brand	AttaBox
Item	Enclosure
Series	Heartland SL
Subpanel	Purchase subpanel separately
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	1/3R/4/4X/6P/12
IP Rating	IP66
Nominal Enclosure Dimensions	12 x 10 x 4in (HxWxD)
Enclosure Height	13.41in
Enclosure Width	11.41in
Enclosure Depth	5.38in

Mounting	Wall
Integral Mounting Feet	Yes
Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	Polycarbonate
Color	Pantone 7541 C light gray
Cover Type	Hinged screw cover
Shelf	No
Padlockable	Yes
Keylocking	No
Additional Information	Mounting hardware

Agency Approvals

UL Listed File #	E319779
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/AH12104HW.pdf>
See store item page for other formats.