

AHF12106 Cut Sheet



AttaBox Heartland series enclosure, NEMA 1/3R/4/4X/12, 12 x 10 x 6in (HxWxD), wall mount, polycarbonate, Pantone 7541 C light gray, single-door, polycarbonate quick-release latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AHF12106>

Technical Specifications

Brand	AttaBox	Integral Mounting Feet	No
Item	Enclosure	Integral Mounting Flange	No
Series	Heartland	Dual Access	No
Subpanel	Purchase subpanel separately	Knockouts	No
Slope Top	No	Bottom Gland Plate	No
3-Piece Assembly	No	Material	Polycarbonate
Vented	No	Color	Pantone 7541 C light gray
NEMA Rating	1/3R/4/4X/12	Cover Type	Single-door
IP Rating	IP66	Latch Type	Polycarbonate quick-release latch
Nominal Enclosure Dimensions	12 x 10 x 6in (HxWxD)	Number Of Latches	2
Enclosure Height	13.41in	Padlockable	Yes
Enclosure Width	11.41in	Keylocking	No
Enclosure Depth	7.38in	Includes	Mounting flanges and hardware
Mounting	Wall		

Agency Approvals

UL Listed File #	E319779
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document