

AJN16-1-CD Cut Sheet

NITRA pneumatic air jet nozzle, 1in length, compound angle, brass.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AJN16-1-CD>

Technical Specifications

Brand	NITRA
Item	Air jet nozzle
Working Fluid	Air or inert gas
Length	1in
Shape	Compound angle
Flow Coefficient	0.1
Material	Brass
Pressure Range	0-125 psi
Operating Temperature	-20 to 160 degrees F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/AJN16-1-CD.pdf>
See store item page for other formats.