

AR22WR-122BZA Cut Sheet



Fuji Electric selector switch, 22mm, 3-position, spring return to center from right or left, (2) N.O./ (2) N.C. contact(s), plastic base, metal bezel, Operator: black, lever, 30mm, round, plastic.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AR22WR-122BZA>

Technical Specifications

Brand	Fuji Electric
Item	Selector switch
Barrel Size	22mm
IP Rating	IP65
Number Of Positions	3
Action	Spring return to center from right or left
Contact Type	(2) N.O./ (2) N.C.
Base Material	Plastic
Bezel Material	Metal
Operator Color	Black
Operator Type	Lever
Operator Size	30mm
Operator Shape	Round
Operator Material	Plastic

Agency Approvals

UL Listed File #	E44592
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR20479
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/AR22WR-122BZA.pdf>
See store item page for other formats.