

# AR30A0N-A0A0BZC Cut Sheet



Fuji Electric selector switch, IP65, 30mm, 2-position, maintained, (2) N.O. contact(s), plastic base, metal bezel, Operator: black, joystick, 41mm, round, plastic.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AR30A0N-A0A0BZC>

## Technical Specifications

Brand	Fuji Electric
Item	Selector switch
Barrel Size	30mm
IP Rating	IP65
Number Of Positions	2
Action	Maintained
Contact Type	(2) N.O.
Base Material	Plastic
Bezel Material	Metal
Operator Color	Black
Operator Type	Joystick
Operator Size	41mm
Operator Shape	Round
Operator Material	Plastic
Connection	Screw terminals

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E44592
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	LR20479
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>