


AR30PR-711BZC Cut Sheet



Fuji Electric selector switch, 30mm, 3-position, spring return from right to center / manual return from left to center, (1) N.O./ (1) N.C. contact(s), plastic base, metal bezel, Operator: black, knob, 35mm, round, plastic.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AR30PR-711BZC>

Technical Specifications

Brand	Fuji Electric
Item	Selector switch
Barrel Size	30mm
IP Rating	IP65
Number Of Positions	3
Action	Spring return from right to center / manual return from left to center
Contact Type	(1) N.O./ (1) N.C.
Base Material	Plastic
Bezel Material	Metal
Operator Color	Black
Operator Type	Knob
Operator Size	35mm
Operator Shape	Round
Operator Material	Plastic

Agency Approvals

UL Listed File #	E44592
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR20479
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document