

# AR30VPL-12E3R Cut Sheet



Fuji Electric emergency stop pushbutton, IP65, 30mm, push to lock, turn to reset, LED illuminated, (1) N.O./(2) N.C. contact(s), plastic base, metal bezel, silver, Operator: red, mushroom, 44mm, mushroom, plastic, 24 VAC/VDC, full voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AR30VPL-12E3R>

## Technical Specifications

Brand	Fuji Electric
Item	Emergency stop pushbutton
IP Rating	IP65
Barrel Size	30mm
Action	Push to lock, turn to reset
Bulb Type	LED illuminated
Contact Type	(1) N.O./(2) N.C.
Base Material	Plastic
Bezel Material	Metal

Bezel Color	Silver
Operator Color	Red
Operator Type	Mushroom
Operator Size	44mm
Operator Shape	Mushroom
Operator Material	Plastic
Operator Legend	Arrow
Voltage Rating	24 VAC/VDC
Voltage Regulation	Full voltage

## Agency Approvals

UL Listed File #	E44592
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/AR30VPL-12E3R.pdf>  
See store item page for other formats.