

ASD-32-24D Cut Sheet



NITRA soft start valve, 3-port (3-way), 2-position, single solenoid spring return, N.C., 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), 3/8in female NPT exhaust(s), Cv=12, 24 VDC operating voltage. For use with Ax-32 series air prep components.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ASD-32-24D>

Technical Specifications

Brand	NITRA	Outlet Port	1/4in female NPT
Item	Valve	Exhaust Port	3/8in female NPT
Working Fluid	Air	Flow Coefficient	12
Valve Type	Soft start	Operating Voltage	24 VDC
Action	Single solenoid spring return	Electrical Connection	DIN style wiring connector
Port Quantity	3-port (3-way)	Indicating Type	LED indication
Number Of Positions	2	For Use With	Ax-32 series air prep components
Valve Configuration	N.C.	Includes	T-bracket
Inlet Port	1/4in female NPT		

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/ASD-32-24D.pdf>
See store item page for other formats.