

ASRB-22-350-1 Cut Sheet



Penn-Union open splicer/reducer block, finger-safe, 620A, 1-pole, line side: 2 openings accept 350 MCM to 6 AWG Cu/AL, load side: 2 openings accept 350 MCM to 6 AWG Cu/AL, DIN rail or panel mount, UL 1953 listed.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ASRB-22-350-1>

Technical Specifications

Brand	Penn-Union
Item	Splicer/reducer block
Terminal Block Type	Open
Modular	Yes
Finger-safe	Yes
Amperage Rating	620A
Number of Poles	1

Line Side Openings	2 openings accept 350 MCM to 6 AWG Cu/AL
Load Side Openings	2 openings accept 350 MCM to 6 AWG Cu/AL
Mounting	DIN rail or panel
SCCR Rating	100kA SCCR
UL Rating	UL 1953 listed
IP Rating	IP20
Additional Information	Suitable for branch and feeder circuits

Agency Approvals

UL Listed File #	E534364
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/ASRB-22-350-1.pdf>
See store item page for other formats.