

AVS-537D2-HL Cut Sheet



NITRA pneumatic manual valve, 5-port (4-way), 2-position, 90 deg hand lever, detented, 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), Cv=1.39, panel or surface mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AVS-537D2-HL>

Technical Specifications

Brand	NITRA
Item	Valve
Working Fluid	Air or inert gas
Valve Type	Manual directional control
Port Quantity	5-port (4-way)
Number Of Positions	2
Operator Type	90 deg hand lever
Action	Detented
Mounting	Panel or surface
Inlet Port	1/4in female NPT
Outlet Port	1/4in female NPT
Stackable	No
Flow Coefficient	1.39

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/AVS-537D2-HL.pdf>
See store item page for other formats.