

# B302409CH Cut Sheet



Wiegmann enclosure, NEMA 12, 30 x 24 x 9in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, (2) plated steel clamps.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/B302409CH>

## Technical Specifications

|                                     |                              |
|-------------------------------------|------------------------------|
| <b>Brand</b>                        | Wiegmann                     |
| <b>Item</b>                         | Enclosure                    |
| <b>Subpanel</b>                     | Purchase subpanel separately |
| <b>Slope Top</b>                    | No                           |
| <b>NEMA Rating</b>                  | 12                           |
| <b>Nominal Enclosure Dimensions</b> | 30 x 24 x 9in (HxWxD)        |
| <b>Enclosure Height</b>             | 30.31in                      |
| <b>Enclosure Width</b>              | 24.50in                      |
| <b>Enclosure Depth</b>              | 9.24in                       |
| <b>Mounting</b>                     | Wall                         |
| <b>Integral Mounting Feet</b>       | No                           |
| <b>Integral Mounting Flange</b>     | Yes                          |

|                                  |                         |
|----------------------------------|-------------------------|
| <b>Dual Access</b>               | No                      |
| <b>Knockouts</b>                 | No                      |
| <b>Material</b>                  | Carbon steel            |
| <b>Color</b>                     | ANSI 61 gray            |
| <b>Finish</b>                    | Powder coat             |
| <b>Cover Type</b>                | Single-door             |
| <b>Hinge Type</b>                | Continuous hinge        |
| <b>Number of Hinges Per Door</b> | 1                       |
| <b>Latch Type</b>                | (2) plated steel clamps |
| <b>Padlockable</b>               | No                      |
| <b>Keylocking</b>                | No                      |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E64791                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |