

# BCCMM603-3PQ Cut Sheet



Bussmann modular combination fuse block, accepts (1) Class Midget and (2) Class CC fuses, 30A, 600V, 3-pole, 18-10 AWG copper only, pressure plate with quick-connect terminals, 35mm DIN rail or panel mount. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BCCMM603-3PQ>

## Technical Specifications

|                             |                                   |
|-----------------------------|-----------------------------------|
| <b>Brand</b>                | Bussmann                          |
| <b>Item</b>                 | Combination fuse block            |
| <b>Modular</b>              | Yes                               |
| <b>Blown Fuse Indicator</b> | No                                |
| <b>Multi-Wire</b>           | No                                |
| <b>Accepts Fuse Class</b>   | (1) Class Midget and (2) Class CC |
| <b>Amperage Rating</b>      | 30A                               |
| <b>Voltage Rating</b>       | 600V                              |
| <b>Number of Poles</b>      | 3                                 |

|                                  |   |
|----------------------------------|---|
| <b>Conductor Size</b>            | 18-10 AWG copper only                       |
| <b>Conductor Connection Type</b> | Pressure plate with quick-connect terminals |
| <b>SCCR Rating</b>               | 200kA SCCR                                  |
| <b>Fuse Connection Type</b>      | Clip with reinforced spring                 |
| <b>Mounting</b>                  | 35mm DIN rail or panel                      |
| <b>Quantity per Pack</b>         | 5   |
| <b>Additional Information</b>    | Covers sold separately                      |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | E14853                                 |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | 47235-6225-01                          |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |
| <b>Other</b>                | None                                   |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/BCCMM603-3PQ.pdf>  
See store item page for other formats.