

BCM603-1PQ-1 Cut Sheet



Bussmann modular fuse block, accepts CC fuses, 30A, 600V, 1-pole, 18-10 AWG copper only, pressure plate with quick-connect terminals, 35mm DIN rail or panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BCM603-1PQ-1>

Technical Specifications

Brand	Bussmann	Number of Poles	1
Item	Fuse block	Conductor Size	18-10 AWG copper only
Modular	Yes	Conductor Connection Type	Pressure plate with quick-connect terminals
Blown Fuse Indicator	No	SCCR Rating	200kA SCCR
Multi-Wire	No	Fuse Connection Type	Clip with reinforced spring
Accepts Fuse Class	CC	Mounting	35mm DIN rail or panel
Amperage Rating	30A	Additional Information	Covers sold separately
Voltage Rating	600V		

Agency Approvals

UL Listed File #	E14853
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	47235-6225-02
RoHS Status	No
EU REACH	View EU REACH document
Other	None