

BLU-030D-2TC38-1 Cut Sheet



Penn-Union BLU series compression lug, standard barrel, tin-plated copper, 35 kV, 3/8in mounting bolt, 2 hole, 1in hole spacing, 300 MCM, white markings.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BLU-030D-2TC38-1>

Technical Specifications

Brand	Penn-Union
Series	BLU
Item	Compression lug
Lug Type	Standard barrel
Material	Tin-plated copper
Voltage Rating	35 kV
Number Of Openings	1

Conductor Material	Copper
Conductor Size	300 MCM
Mounting Bolt Size	3/8in
Mounting Holes	2 hole
Mounting Hole Spacing	1in
Inspection Window	Yes
Marking Color	White

Agency Approvals

UL Listed File #	E12822
UL Recognized File #	none
UL Hazardous File #	none
CSA File #	167436
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/BLU-030D-2TC38-1.pdf>
See store item page for other formats.