

BLU-1D-2TC14-1 Cut Sheet



Penn-Union BLU series compression lug, standard barrel, tin-plated copper, 35 kV, 1/4in mounting bolt, 2 hole, 0.63in hole spacing, 1 AWG, green markings.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BLU-1D-2TC14-1>

Technical Specifications

| | |
|---------------------------|-------------------|
| Brand | Penn-Union |
| Series | BLU |
| Item | Compression lug |
| Lug Type | Standard barrel |
| Material | Tin-plated copper |
| Voltage Rating | 35 kV |
| Number Of Openings | 1 |

| | |
|------------------------------|--------|
| Conductor Material | Copper |
| Conductor Size | 1 AWG |
| Mounting Bolt Size | 1/4in |
| Mounting Holes | 2 hole |
| Mounting Hole Spacing | 0.63in |
| Inspection Window | Yes |
| Marking Color | Green |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E12822 |
| UL Recognized File # | none |
| UL Hazardous File # | none |
| CSA File # | 167436 |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/BLU-1D-2TC14-1.pdf>
See store item page for other formats.