

# BLU-8D-2TC14-1 Cut Sheet



Penn-Union BLU series compression lug, standard barrel, tin-plated copper, 35 kV, 1/4in mounting bolt, 2 hole, 0.63in hole spacing, 8 AWG, red markings.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BLU-8D-2TC14-1>

## Technical Specifications

<b>Brand</b>	Penn-Union
<b>Series</b>	BLU
<b>Item</b>	Compression lug
<b>Lug Type</b>	Standard barrel
<b>Material</b>	Tin-plated copper
<b>Voltage Rating</b>	35 kV
<b>Number Of Openings</b>	1

<b>Conductor Material</b>	Copper
<b>Conductor Size</b>	8AWG
<b>Mounting Bolt Size</b>	1/4in
<b>Mounting Holes</b>	2 hole
<b>Mounting Hole Spacing</b>	0.63in
<b>Inspection Window</b>	Yes
<b>Marking Color</b>	Red

## Agency Approvals

<b>UL Listed File #</b>	E12822
<b>UL Recognized File #</b>	none
<b>UL Hazardous File #</b>	none
<b>CSA File #</b>	167436
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/BLU-8D-2TC14-1.pdf>  
See store item page for other formats.