

BMEM-E4-M32T-WCL Cut Sheet



Bimed EMC cable gland, M32 x 1.5mm thread type, nickel-plated brass, accepts 16 to 25mm diameter cable, IP68. Package of 5. Mounting hardware included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BMEM-E4-M32T-WCL>

Technical Specifications

| | |
|--------------------------|---------------------|
| Brand | Bimed |
| Item | Cable gland |
| Application | EMC |
| Thread Type | M32 x 1.5mm |
| Material | Nickel-plated brass |
| Cable OD Range | 16 to 25mm |
| Shield OD Range | 12 to 20mm |
| IP Rating | IP68 |
| Strain Relief | No |
| Quantity per Pack | 5 |
| Includes | Mounting hardware |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E199260 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes with Exemptions (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/BMEM-E4-M32T-WCL.pdf>
See store item page for other formats.