

BN4060403SS Cut Sheet



Wiegmann enclosure, NEMA 4/4X/12/13, 6 x 4 x 3in (HxWxD), wall mount, 304 stainless steel, No. 3 intermediate polished finish, lift-off cover, (4) stainless steel clamps.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BN4060403SS>

Technical Specifications

| | |
|-------------------------------------|------------------------------|
| Brand | Wiegmann |
| Item | Enclosure |
| Subpanel | Purchase subpanel separately |
| Slope Top | No |
| NEMA Rating | 4/4X/12/13 |
| IP Rating | IP66 |
| Nominal Enclosure Dimensions | 6 x 4 x 3in (HxWxD) |
| Enclosure Height | 6.31in |
| Enclosure Width | 4.31in |
| Enclosure Depth | 3.31in |
| Mounting | Wall |
| Integral Mounting Feet | No |
| Integral Mounting Flange | Yes |
| Dual Access | No |
| Knockouts | No |
| Material | 304 stainless steel |
| Finish | No. 3 intermediate polished |
| Cover Type | Lift-off cover |
| Latch Type | (4) stainless steel clamps |
| Padlockable | No |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E23553, E64791 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |