


BN4060604AL Cut Sheet



Wiegmann enclosure, NEMA 4/4X/12/13, 6 x 6 x 4in (HxWxD), wall mount, 5052-H32 aluminum, No. 3 intermediate polished finish, lift-off cover, (4) stainless steel clamps.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BN4060604AL>

Technical Specifications

Brand	Wiegmann
Item	Enclosure
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	4/4X/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	6 x 6 x 4in (HxWxD)
Enclosure Height	6.31in
Enclosure Width	6.31in
Enclosure Depth	4.26in
Mounting	Wall
Integral Mounting Feet	No
Integral Mounting Flange	Yes
Dual Access	No
Knockouts	No
Material	5052-H32 aluminum
Finish	No. 3 intermediate polished
Cover Type	Lift-off cover
Latch Type	(4) stainless steel clamps
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E6924, E23553
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document