

BN4161406SSA Cut Sheet



Wiegmann enclosure, NEMA 4/4X/12/13, 16 x 14 x 6in (HxWxD), wall mount, 316L stainless steel, No. 3 intermediate polished finish, lift-off cover, (10) stainless steel clamps.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BN4161406SSA>

Technical Specifications

| | |
|---------------------------------|------------------------------|
| Brand | Wiegmann |
| Item | Enclosure |
| Subpanel | Purchase subpanel separately |
| Slope Top | No |
| NEMA Rating | 4/4X/12/13 |
| IP Rating | IP66 |
| Nominal Enclosure Height | 16in |
| Nominal Enclosure Width | 14in |
| Nominal Enclosure Depth | 6in |
| Mounting | Wall |

| | |
|---------------------------------|-----------------------------|
| Integral Mounting Feet | No |
| Integral Mounting Flange | Yes |
| Dual Access | No |
| Knockouts | No |
| Material | 316L stainless steel |
| Finish | No. 3 intermediate polished |
| Cover Type | Lift-off cover |
| Latch Type | (10) stainless steel clamps |
| Padlockable | No |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E23553, E64791 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BN4161406SSA.pdf>
See store item page for other formats.