BR-N1-4K7W14P7 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

Crohm braking resistor, 4.7 kW, 14.7 ohm, NEMA 1, built-in temperature switch. For use with multiple AC drives.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/BR-N1-4K7W14P7

Technical Specifications

Brand	Crohm
Item	Braking resistor
Brake Resistor Power Rating	4.7 kW
Resistance	14.7 ohm
Enclosure Type	NEMA 1
Built-in Temperature Switch	Yes
For Use With	Multiple AC drives

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	303117
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/BR-N1-4K7W14P7.pdf
See store item page for other formats.