

# BRY24W34 Cut Sheet



Bryant watertight locking blade plug, 15A, 277 VAC, 1-phase, 2-pole, 3-wire, NEMA L7-15, accepts cord size 0.3-0.62in, UL Type 4, 4X, 6 and 6P, thermoplastic elastomer (PTE) housing, yellow.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BRY24W34>

## Technical Specifications

Brand	Bryant
Item	Plug
Application	Watertight
Blade Type	Locking
With Cap	No
Amperage Rating	15A
Voltage Rating	277 VAC
Number of Phases	1

Number of Poles	2
Number of Wires	3
Wire Size	18-12 AWG
Configuration	NEMA L7-15
Cord Diameter	0.3-0.62in
UL Type	4, 4X, 6 and 6P
Housing Material	Thermoplastic elastomer (PTE)
Color	Yellow

## Agency Approvals

UL Listed File #	E1706
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	1284294
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/BRY24W34.pdf>  
See store item page for other formats.