

# BRY24W47 Cut Sheet



Bryant watertight locking blade plug, 15A, 125 VAC, 1-phase, 2-pole, 3-wire, NEMA L5-15, accepts cord size 0.3-0.62in, UL Type 4, 4X, 6 and 6P, thermoplastic elastomer (PTE) housing, yellow.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BRY24W47>

## Technical Specifications

<b>Brand</b>	Bryant
<b>Item</b>	Plug
<b>Application</b>	Watertight
<b>Blade Type</b>	Locking
<b>With Cap</b>	No
<b>Amperage Rating</b>	15A
<b>Voltage Rating</b>	125 VAC
<b>Number of Phases</b>	1
<b>Number of Poles</b>	2
<b>Number of Wires</b>	3
<b>Wire Size</b>	18-12 AWG
<b>Configuration</b>	NEMA L5-15
<b>Cord Diameter</b>	0.3-0.62in
<b>UL Type</b>	4, 4X, 6 and 6P
<b>Housing Material</b>	Thermoplastic elastomer (PTE)
<b>Color</b>	Yellow

## Agency Approvals

<b>UL Listed File #</b>	E1706
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	1284294
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>