

# BRY26W48 Cut Sheet



Bryant watertight locking blade plug, 20A, 250 VAC, 1-phase, 2-pole, 3-wire, NEMA L6-20, accepts cord size 0.325-0.75in, UL Type 4, 4X, 6 and 6P, thermoplastic elastomer (PTE) housing, yellow.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BRY26W48>

## Technical Specifications

Brand	Bryant
Item	Plug
Application	Watertight
Blade Type	Locking
With Cap	No
Amperage Rating	20A
Voltage Rating	250 VAC
Number of Phases	1
Number of Poles	2
Number of Wires	3
Wire Size	18-10 AWG
Configuration	NEMA L6-20
Cord Diameter	0.325-0.75in
UL Type	4, 4X, 6 and 6P
Housing Material	Thermoplastic elastomer (PTE)
Color	Yellow

## Agency Approvals

UL Listed File #	E1706
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	1284294
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>