

BRY26W75 Cut Sheet



Bryant watertight locking blade plug, 20A, 250 VAC, 3-phase, 3-pole, 4-wire, NEMA L15-20, accepts cord size 0.325-0.875in, UL Type 4, 4X, 6 and 6P, thermoplastic elastomer (PTE) housing, yellow.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BRY26W75>

Technical Specifications

Brand	Bryant
Item	Plug
Application	Watertight
Blade Type	Locking
With Cap	No
Amperage Rating	20A
Voltage Rating	250 VAC
Number of Phases	3

Number of Poles	3
Number of Wires	4
Wire Size	18-10 AWG
Configuration	NEMA L15-20
Cord Diameter	0.325-0.875in
UL Type	4, 4X, 6 and 6P
Housing Material	Thermoplastic elastomer (PTE)
Color	Yellow

Agency Approvals

UL Listed File #	E1706
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	1284294
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BRY26W75.pdf>
See store item page for other formats.