

BRY320C4W Cut Sheet



Bryant watertight pin and sleeve connector, 20A, 125 VAC, 1-phase, 2-pole, 3-wire, 4 hour, accepts cord size 0.37-0.595in, IP67, nylon housing, yellow.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BRY320C4W>

Technical Specifications

Brand	Bryant
Item	Connector
Application	Watertight
Wiring Device Type	Pin and sleeve
With Cap	No
Amperage Rating	20A
Voltage Rating	125 VAC
Number of Phases	1
Number of Poles	2

Number of Wires	3
Wire Size	14-12 AWG
Configuration	4 hour
Cord Diameter	0.37-0.595in
IP Rating	IP67
Housing Material	Nylon
Color	Yellow
Manufacturer Part Number	C320C4WA

Agency Approvals

UL Listed File #	E146033
CE	View CE declarations
CSA File #	N/A
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/BRY320C4W.pdf>
See store item page for other formats.